





3P~15P Shape

2P Shape



Specifications :

- Voltage rating: 500V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥500MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤30mΩ

X 8821 H X L X-N0

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: H-HSG
- ③ Appearance type: Blank-ordinary
- ④ Row No.-Pin No.: XX-Single Row
- ⑤ Plug the Pin & Special No. : L-With Lock
- ⑥ Material : N0-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.50	5.70	09	20.00	25.00	23.20
03	5.00	10.00	8.20	10	22.50	27.50	25.70
04	7.50	12.50	10.70	11	25.00	30.00	28.20
05	10.00	15.00	13.20	12	27.50	32.50	30.70
06	12.50	17.50	15.70	13	30.00	35.00	33.20
07	15.00	20.00	18.20	14	32.50	37.50	35.70
08	17.50	22.50	20.70	15	35.00	40.00	38.20

X8821H-XXL-N0	Nylon 66 UL 94V-0	x8821T-L	x8821W-L
PART N0	Material	Suitable SWB Terminal	Mates With XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connector		
ΔX					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:		
ΔX					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm	DWG NO.: X 8821H-XXL-N 2		
ΔX					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4			
ΔX					16<L ≤ 63	±0.4								
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L > 63							
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														
												WEIGHT	SHEET	REVISION
												1.0g	1/1	A0