








Lötanschluss 0,6 x 0,6 / solder terminal 0,6 x 0,6
 Isolierwerkstoff / housing material: PBT GF 30
 Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
 Bauart 7 / type 7

Leiterplatten-Layout Vorschlag PCB-Layout proposal



Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 9016 to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale		2:1			
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation Federleiste D 32 Löt <i>Fem Connector D 32 Solder</i>					
				ERNI		www.ERNI.com		354647				I	
a		07.05.2013								A3			
Index		Date								Class		STVD	

Fehlende Masse und Angaben nach DIN EN 60603-2 / Missing information and dimensions according to DIN EN 60603-2
 Sonstige Angaben siehe Fertigungsunterlagen / Additional indications please see the production documentation