



300V 5A 20-18AWG 1.5mm²

Poles: 1P-XXP

Pitch: 5.0mm (.197") / 5.08mm (.200")

Materials

Housing: PA66 (UL 94V-0)

Solder Pin: Brass, Tin Plated

Clamping: stainless steel

设计/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		未注公差 General Tolerance	
								X. ° ±2°	
图名/File name		文件编号/File No.						.X ±0.1 .X° ±1°	
XY119A								.XX ±0.05 .XX° ±0.5°	
XY119B				页序/Sheet				.XXX ±0.01	
备注/Remark								单位/Units: mm	
 XINLAIYA ELECTRONIC CO., LTD									