


带@符号为重点尺寸,



PART NO	Dim. A	Dim. B
MFC-8P	6.0	13.2
MFC-10P	8.0	15.2
MFC-12P	10.0	17.2
MFC-14P	12.0	19.2
MFC-16P	14.0	21.2
MFC-18P	16.0	23.2
MFC-20P	18.0	25.2
MFC-22P	20.0	27.2
MFC-24P	22.0	29.2
MFC-26P	24.0	31.2
MFC-28P	26.0	33.2
MFC-30P	28.0	35.2
MFC-34P	32.0	39.2
MFC-36P	34.0	41.2
MFC-40P	38.0	45.2
MFC-44P	42.0	49.2
MFC-50P	48.0	55.2
MFC-56P	54.0	61.2



**MATERIAL&FINISH**

"H" Insulator: PBT Glass Fiber(UL94V-0)  
 "M" Insulator: PA66 Glass Fiber(UL94V-0)  
 "SR" Insulator: PA66 Glass Fiber(UL94V-0)  
 Contact : Brass  
 Contact : Gold-Plated Over Nickel.

**SPECIFICATIONS**

Current Rating :1A AC,DC  
 Voltage Rating : 250V AC,DC  
 Temperature Range:-40° C To+105° C  
 Contact Resistance:20mΩ Min  
 Insulation Resistance:1000MΩ Min  
 Withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE : .X ±0.25 ANGLES : ±2° .XX ±0.15 .XXX ±0.10 DO NOT SCALE DRAWING		深圳市威电康精密科技有限公司	
DRAWN BY	唐建华	TITLE 2.0/MFC成品图	
CHECKED BY		SIZE A	UNIT MM
APPROVED BY		PART NO. CSD-WI-EG-OA-003	
DWG NO.		THIRD ANGLE PROJECTION	
		ITEM NO.	
		REV A	
		PAGE 1 OF 1	
		DATE 09/07/2006	