



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2510 H -XX -N0

① ② ③ ④

- ① Series No.
- ② Category: H-HSG
- ③ Row No.-Pin No.:XX-Single row
- ④ Material: N0-PA66 94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.54	5.08	10	22.86	26.12
03	5.08	8.34	11	25.4	28.66
04	7.62	10.88	12	27.94	31.2
05	10.16	13.42	13	30.48	33.74
06	12.7	15.96	14	33.02	36.28
07	15.24	18.5	15	35.56	38.82
08	17.78	21.04			
09	20.32	23.58			

X2510H-XX-N0	Nylon 66 UL 94V-0	X2510T	X2510W
PART NO	Material	Suitable SWB Terminal	Mates With XKB Wafer

DSND	DATE	SCALE: N/A	MODEL TYPE: 2510H-XX-N2
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm	2.54 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△ X					ANGULAR ±5°
△ X					L ≤ 4 ±0.2
△ X					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
			1.0g	1/1	A0

REVISIONS
Authorized Signature(s)