



PowerSync®
包尔星克



10A 三插90度公对母电源延长线

- 线材通过3C认证
- 抗摇摆设计，耐弯折
- 原产地:中国上海
- 纯铜线芯，阻燃线材，耐高温
- 安全/耐热 采用RVV耐热线材

型号	长度/m	线材规格	外被线径/mm
MPCTKP0010	1.0	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0015	1.5	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0020	2.0	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0030	3.0	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0050	5.0	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0100	10	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0150	15	RVV 1.5mm ² x3C	9.4+0/-0.4
MPCTKP0200	20	RVV 1.5mm ² x3C	9.4+0/-0.4

9.4+0/-0.4