



**PowerSync®**  
包尔星克



## 直头电脑主机电源线

- 线材通过3C认证
- 标准国标三插直头对品字尾
- 纯铜线芯，导电性好，RVV耐热线材安全实用
- PVC外被材质,韧度好,不易受外力拉扯断
- 原产地:中国上海

| 型号       | 长度/m | 线材规格                        | 外被线径/mm |
|----------|------|-----------------------------|---------|
| MPPD0005 | 0.5  | RVV 0.75mm <sup>2</sup> x3C | 6.7±0.2 |
| MPPD0010 | 1.0  | RVV 0.75mm <sup>2</sup> x3C | 6.7±0.2 |
| MPPD0015 | 1.5  | RVV 0.75mm <sup>2</sup> x3C | 6.7±0.2 |
| MPPL0005 | 0.5  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0010 | 1.0  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0015 | 1.5  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0020 | 2.0  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0030 | 3.0  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0050 | 5.0  | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |
| MPPL0100 | 10   | RVV 1.0mm <sup>2</sup> x3C  | 7.0±0.2 |