







SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:30mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃


Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PBT
Max.Processing Temp: 180℃ for 30-60 seconds
(200℃ for 10 seconds)



Ordering Information

3511 2 XX B F S XX BNA1

No. of Pins 16~64P
Contact Type F=Female
Contact Plating
G0:Gold Flash
S3:10U" Gold
S4:15U" Gold
S5:30U" Gold
S0:Gold Flash/Tin
SN:Tin



Dimension antitheses list	
ITEM	A
Standard	4.00
Alternate	

OPERATION		DRAW		SCALE		FIT	PART NO.	TITLE:
X.X	±0.30	YYuSheng	14.09.16	UNIT	mm			
X.XX	±0.20	CHECK		SIZE	A4	1/1	3511-2XXBFSXXBNA1	欧式插座 母座 180度 2xPIN 成品系列图
X.XXX	±0.10	APPROVE		SHEET				
Angle	±3°			PROJ.				
DIM	TOL							
CHANGE								
MODIFICATION DESCRIPTION								
DATE								
REV								
A0	NEW DRAWING							
2012.04.10								
2014.09.16	增加U1标识							

JIN 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONIC CO.,LTD
Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892