








SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:30mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(Ul94V-0)
Standard: PBT
Max.Processing Temp: 180℃ for 30-60 seconds
(200℃ for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

Dimension antitheses list	
ITEM	A
Standard	2.90
Alternate	

Ordering Information

3511 3 32 C F R S0 B N A 2

No.of Pins 64PIN
Contact Type F=Female
Contact Plating 60:60d Flash
S2:2U" Gold
S3:10U" Gold
S4:15U" Gold
S5:30U" Gold
S0:60d Flash/Tin
SN:Tin
Packing A=Tray
T=Tube

						OPERATION		DRAW		YTuSheng		14.09.16		SCALE		FIT		jiln® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONIC CO.,LTD Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992			
						X.X		±0.30						UNIT		mm					
						X.XX		±0.20		CHECK				SIZE		A4					
B		2014.09.16		增加UL标识		X.XXX		±0.10						SHEET		1/1					
A0		2012.04.10		NEW DRAWING										PROJ.				PART NO.		3511332CFRS0BNA2	
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		DIM		TOL		APPROVE						TITLE:		卧式插座 母座 90度 332(A+C) 成品图	
1		2		3		4		5		6		7		8		9					

JILIN 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONIC CO.,LTD
Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

款式插座 母座 90度 332(A+C) 成品图