






| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | |
|----------------|---|---|---|---|---|---|---|---|----|----|------|--------------|------|------|---------|
| ROHS Compliant | | | | | | | | | | | MAPX | MODIFICATION | DATE | DRAW | APPROVE |



RECOMMENDED P.C.B LAYOUT

备注:

- 1.产品规格:
 - 1-1.插拔力: 35N MAX.
 - 1-2.拔出力: 10N MIN. INITIAL 8-20N
 - 1-3.额定电流: 1.0A
 - 1-4.额定电压: 30V
 - 1-5.耐久性: 3,000 CYCLES MIN.
 - 1-6.耐电压: 100V AC MIN.
 - 1-7.接触阻抗: 30mΩ MAX. INITIAL 40mΩ MAX
 - 1-8.绝缘电阻: 100MΩ MIN
 - 1-9.工作温度: -30°C TO +80°C
- 2.材质:
 - 2-1.胶芯: LCP UL94V-0
 - 2-2.端子: C5191, 镍底, 镀金1u"
 - 2-3外壳: SUS
- 3.所用材质须符合ROHS要求

| | |
|--|---|
| MANUFACTURE DWG |  DongGuan XunPu Electronics Co,Ltd |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |  |
| DECIMALS: | ANGLES: |
| X:±0.35 | X:±2° |
| X:±0.25 | X:±1° |
| XX:±0.15 | XX:±0.5° |
| CUSTOMER COPY | SCALE 1:1 UNIT: mm |
| SIZE:A4 SHEET:1F1 | REV:A |

TITLE: MICRO 180° B型母座直插
无卷边加长

PAR MU-106-ARWH20

DWN KING 2018.06.17

CHKD

APVD

SCALE 1:1 UNIT: mm

SIZE:A4 SHEET:1F1 REV:A