





RoHS

SPECIFICATIONS

Rated Current:1.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c
 Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Alternate	4.00	2.50	9.50

深圳市连盛精密连接器有限公司

OPERATION	DRAW	SCALE	FIT
X.X		UNIT	mm
X.XX	±0.30	SIZE	A4
X.XXX	±0.20	SHEET	1/1
X.XXX	±0.10	PROJ.	
Angle	±3°		
DIM	TOL		

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.04.19	NEW DRAWING	
1			

PART NO.	TITLE:
PH-00555 ---C0007	1.27PH 2x5Pin 2H=2X1.5mm