





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PBT
 Max.Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

深圳市连盛精密连接器有限公司

REV		DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	OPERATION	SCALE	FIT	PART NO.		TITLE:	
A0		2012.03.28	NEW DRAWING				X.X ±0.30	UNIT	mm	PH-00219		2.54PH H2.5mm 2x3P 180°	
							X.XX ±0.20	SIZE	A4				
							X.XXX ±0.10	SHEET	1/1				
							Angle ±3°	PROJ.	☯				