

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40℃ to +105℃


Contact Material:Brass

Contact Plating:Au Over Ni




Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ± 0.30

DRAW

UNIT

mm

X.XX ± 0.20

CHECK

SIZE

A4

X.XXX ± 0.10

CHECK

SHEET

1/1

Angle $\pm 3^\circ$

APPROVE

PROJ.

1/1

PART NO.

BH-00312

TITLE:

2.0Box Npin H5.65 SMT

REV DATE MODIFICATION DESCRIPTION CHANGE

1

2

3

4

5

6

7

8

9