





RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:400V AC/DC
 Insulation Resistance:800MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au足0.8 Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



				OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm		
						CHECK		SIZE	A4	PART NO.	
				X.XX	±0.20			SHEET	1/1	BH-00319	
A0	2012.03.28	NEW DRAWING				APPROVE		PROJ.	◆	TITLE:	2.0BOX H=5.65 10P DIP
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL					

深圳市连盛精密连接器有限公司

PART NO. BH-00319

TITLE: 2.0BOX H=5.65 10P DIP