

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass





Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list

ITEM	PC	PA	L	TYPE
Alternate	3.00	3.60	11.60	

OPERATION

DRAW

LU

14.04.16

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

CHECK

SIZE

A4

X.XXX ±0.10

CHECK

SHEET

1/1

PART NO.

PH-01303

Angle ±3°

APPROVE

PROJ.

TITLE:

2.54PH 2H=2X2.5 1X8P 180°

A0 2014.04.16

NEW DRAWING

REV DATE

MODIFICATION DESCRIPTION

CHANGE

DIM TOL