


环保物料

TEL:0769-82001899

| 公称尺寸 (mm) | 公差 (±mm) | 一视角 |
|-----------|----------|-----|
| 0--10 | 0.10 | |
| 10--20 | 0.15 | |
| 20--30 | 0.20 | |
| 30--40 | 0.25 | |
| 40--50 | 0.30 | |
| 50 以上 | 0.35 | |
| 角度 | ±1° | |



技术要求:

- 1.表面光滑,无划痕
- 2.材质:铜片:黄铜 T0.8mm
- 3.螺钉拧紧力矩:0.6NM
- 4.额定电流:40A
- 5.表面处理:镀雾锡3-5um
- 6.牙孔规格:M3

| | | | | | | | | | | | |
|-----------|--------------|------|------|----------------------------|-------|-------|--------|--|---------|--------------|------------------------|
| A0 VER | MODIFICATION | DRAW | DATE | TOLERANCE UNLESS OTHERWISE | | DRAWN | CK tan | XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD. | SHEET | 1/1 | |
| | | | | X. | ±0.30 | X° | ±5° | | CHKD | DATE | 2010.4.12 |
| | | | | .X | ±0.20 | .X° | ±2° | | APPD | PRODUCT NAME | PCB Soldering Terminal |
| | | | | .XX | ±0.08 | .XX° | ±1° | | VIEW | PART. NO. | T34080080-0685 |
| | | | | .XXX | ±0.03 | .XXX° | ±0.5° | | DWG NO. | 009 | |