



型号: KH-A1251LF-06A

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated



PCB LAYOUT

| 编号 | 尺寸 (mm) | |
|-------------|---------|-------|
| | A | B |
| A1251LF-02A | 1.25 | 7.35 |
| A1251LF-03A | 2.50 | 8.60 |
| A1251LF-04A | 3.75 | 9.85 |
| A1251LF-05A | 5.00 | 11.10 |
| A1251LF-06A | 6.25 | 12.35 |
| A1251LF-07A | 7.50 | 13.60 |
| A1251LF-08A | 8.75 | 14.85 |
| A1251LF-09A | 10.00 | 16.10 |
| A1251LF-10A | 11.25 | 17.35 |
| A1251LF-11A | 12.50 | 18.60 |
| A1251LF-12A | 13.75 | 19.85 |
| A1251LF-20A | 23.75 | 29.85 |

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | | 制图 DRAWING | 钱岳生 2013.07.01 | 料号 PART NO. | KHA1251LF-NA | 版本 REV. | A |
|-------------|---------------------|------------|-------------------|------------|----------------|-------------------|-------------------|--------------------------|------------------------------|-----|
| | | | X.±0.25 | X.'±2' | 审核 CHECK | 张名 2013.07.03 | 品名 TITLE | 1.25立贴 WAFER SMT TYPE | 页次 SHEET | 1/1 |
| | | | .X±0.20 | .X'±1' | 核准 APPROVAL | 张名 2013.07.05 | 客户料号 CUTM. NO. | | | |
| | | | .XX±0.15 | .XX'±0.5' | 单位 UNITS | MM | 比例 SCALE | 1:1 | 深圳市金航标电子有限公司 | |
| | | | .XXX±0.10 | .XXX'±0.5' | | | | | WWW.BDS666.COM 0755-83044319 | |