





RoHS

REVISIONS

SYM	ECN No.	MODIFICATION	DATE	ISSUED



Note:

1. Material:

- 1.1, Housing: High temperature thermoplastic with/black g.f, UL94v-0
- 1.2, Contact: copper alloy, t=0.25mm
- 1.3, Shell: copper/Ferroalloy alloy, t=0.35mm

2. Specification:

- 2.1, Current rating: 3A Max.
- 2.2, Dielectric withstanding voltage: 100 V(ac) for 1 min.
- 2.3, Contact resistance: 30 mΩ Max.
- 2.4, Insulation resistance: 100 MΩ Min.
- 2.5, Total mating force: 3.57 Kgf Max.
- 2.6, Total unmating force: 1.0 Kgf Min.

3. Finish:

- 3.1, Contact: Plated Gold in Mating Area:  
Tin On Solder Talls  
Shell: Nickel Plating

4. Environmental:

- 4.1, Temperature range: -55°C~85°C

DRAWN		<b>JTJ</b> 深圳市精拓金电子有限公司					
CHECKED		TITLE AM大电流一体式 (大縫隙) PBT绿色		PART NO. 917-111A115DAM0400			
APPROVED				DRAWING NO. --			
 3rd ANGLE PROJECTION	UNIT	TOLERANCE .XXX±.10, .XX±.15, .X±.25, ANG±1°		SCALE	SHEET	SIZE	REV.
	mm			1:1	1 OF 1	A4	X1