



项目	零件名称	数量	材质	处理/备注
1	SHELL	1	STAINLESS	Ni: 50u"
2	Molding HOUSING	2	L.C.P	(Black)
3	GND SPRING	2	STAINLESS	Ni: 50u"
4	Insert molding 12PIN	2	L.C.P	(Black)
5	CONTACT	24	COPPER ALLOY	Contact area: gold flash, Solder tails: Tin100u", Ni: 50u"
6	PCB	1	--	--

; SPECIFICATION

MATERIAL

See drawing

STANDARD DATA

Operating temperature: -10°C ~ +60°C

Storage temperature: -20°C ~ +85°C

ELECTRICAL

Insulator resistance: 100Mohms Min.

Withstanding voltage: 100 VAC / minute

Contact resistance: initial 40mohms Max;  
after 50mohms Max.

MECHANICAL

Mating force: 5~20N

Unmating force : 8~20N

Durability: 5000 cycles Min.

产品图  
PRODUCT CHART DWG

深圳市精拓金电子有限公司

公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.	950-M610E04A4-00		
X.	±0.25	X'	±5'	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NO.	USB Type-C3.1 公头拉伸圆形-5A大电流 56K 双电阻 紫色		
.X	±0.20	.X'	±2'						日期 DATE	2015.07.14	核准 APPD
.XX	±0.15	.XX'	±1'								
.XXX	±0.10	.XXX'	±0.5'								