


RoHS

MAPX


MODIFICATION

DRW

DATE




6.00



0.56

1.84

5.12




15.72

11.5

2.50

1.4

1.5




2.00

4.00

0.40

7.00

8.00



13.14

0.50

8.00

4.00

2.00

ø2.30

1.40

1.50

ø0.70

3.07

7.00

13.14

NOTES:

1.MATERIAL:

- 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC.
- 1.2 SPRING CONTACT: COPPER ALLOY.
- 1.3 FLAT CONTACT;COPPER ALLOY
- 1.4 SHELL :COPPER ALLOY.
- 1.5 COVER:HIGH TEMPERATURE THERAL PLASTIC.

2.FINISH:

- 2.1 CONTACT: (SEE P/N.),[50μ"] MIN. NICKEL UNDERPLATING OVER ALL.
- 2.2 SHELL: [50μ"] MIN.SOLDERABLITY NICKEL UNDERPLATING OVER ALL.

PIN NO.	PIN 1	PIN 2	PIN 3	PIN 4
SLGNL NAME	V BUS	D-	D+	GND
REMARK	USB 2.0 CONTACT PINS			

PIN NO.	PIN 5	PIN 6	PIN 7	PIN 8	PIN 9
SLGNL NAME	STDA_SSRX-	STDA_SSRX+	GND_DRAIN	STDA_SSTX-	STDA_SSTX+
REMARK	USB 3.0 CONTACT PINS				

**产品图**  
PRODUCT CHART DWG

**公差一览表**  
TOLERANCE UNLESS OTHERWISE

X.	±0.25	X.	±5.°
X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.10	.XXX	±0.5°

**深圳市精拓金电子有限公司**  
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	XRQ	制图料号 PRODUCT PART NO.	916-363A205EY10200
比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	USB AF 3.0/180度11.5直脚无边铜壳LCP蓝胶24H
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW	版本 VER