



MAPX	MODIFICATION	DATE

Specifications:

Electrical:

- 1.Current Rating :1.5A/contact terminal
- 2.Voltage Rating :30V DC
- 3.Contact Resistance:30 milliohms MAX
- 4.Dielectric Withstanding Voitage:500 V AC AT Sea Level
- 5.Insulation Resistance:1000MEGA ohms MIN

Mechanical:

- 1.Connector Mate and Unmate Force: Mate force:3.75kgf(MAX)
Unmate force:0.40kgf(MIN)
- 2.Terminal Retention :0.40kgf(MIN)

Material:

- 1.Housing: Hing Temperature Ternmaplastics,
UI 94V-0 LCP White/Black
- 2.Contact:Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area; Tin On Solder Talls
- 2.Shell: Nickel Plating

P.B.T LAYOUT

<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p> <table border="1"> <tr> <td>X.</td> <td>±0.35</td> <td>X.</td> <td>±5.°</td> </tr> <tr> <td>.X</td> <td>±0.30</td> <td>.XX</td> <td>±2.°</td> </tr> <tr> <td>.XX</td> <td>±0.20</td> <td>.XXX</td> <td>±1.°</td> </tr> <tr> <td>.XXX</td> <td>±0.10</td> <td>.XXX</td> <td>±0.5°</td> </tr> </table>				X.	±0.35	X.	±5.°	.X	±0.30	.XX	±2.°	.XX	±0.20	.XXX	±1.°	.XXX	±0.10	.XXX	±0.5°	<p>深圳市精拓金电子有限公司</p>						
X.	±0.35	X.	±5.°																							
.X	±0.30	.XX	±2.°																							
.XX	±0.20	.XXX	±1.°																							
.XXX	±0.10	.XXX	±0.5°																							
单位 UNITS	MM	制图 DRAWING	Gavin	制图料号 PRODUCT PART NO.	920-462A2021Y10103																					
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NAME	MINI/5P 母座立式6.65/7.7无边两脚 全贴带柱LCP 黑胶端子SMT																					
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW		版本 VER	AD																			