



300V 30A 26-10AWG 4.0mm²
 Poles: 2P&3P-24P
 Pitch: 9.5mm (.375")

Materials
 Housing: PA66 (UL 94V-0)
 Solder Pin: Brass, Tin Plated
 Wire Cage: Steel A3, Nickel Plated
 Screw: M3, Steel (A3), Zinc Plated
 Torque: 0.5N.m

| | | | | |
|----------------|--------------------|---------------|----------------|---|
| 设计/Designed by | 绘图/Drawing by | 审核/Checked by | 批准/Approved by | 未注公差 General Tolerance |
| | | | | X: ±0.2 X: ±0.1 .XX ±0.05 .XXX ±0.01 |
| 图名/Title | | 文件编号/File No. | | X: ±2° X: ±1° .XX ±0.5° .XXX ±0.5° |
| XY130-9.5 | | 页序/Sheet | | |
| 备注/Remark | | | | 单位/Units: mm |
| 序号/Revno. | 更改记录/Revision note | 签名/Signature | 日期/Date | |

