



特性: Specifications;
 电器: Electyical:

接触阻抗: Contact Resistance
 30 millionms MAX
 耐电压: Dielectyic Withstanding Voltage:
 500v AC AT Sea Level
 绝缘阻抗: Insulation Resistance:
 1000 MEGA ohms MLN

机构: Machanical:
 接合为: Mating Force;
 4.0 KG MAX 最大4Kg
 拔出力: Unmating Force;
 0.7KG MIN. 最少0.7KG

PART NO	H
U-A-24DD-Y-2	13.00
U-A-24DD-Y-3	13.70
U-A-24DD-Y-4	15.00

Recommended PCB Layout

③	Base	—	1	NYLON	White
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Phosphor Bronze	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	JIANKUN.LU	2015.03.18		TITLE:	USB CONNECTOR	
CHECKED				PART NO.		
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE			30~以上	±0.30	ANGLE	±2'
			10~30	±0.25		
			5~10	±0.20		
			~ 5	±0.15		
				DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			