





SPECIFICATIONS

- 1.Voltage rating: 600V AC, DC
 - 2.Current rating: 9A, AC, DC
 - 3.Withstanding Voltage: 1500V AC/minute
 - 4.Insulation resistance:1000M min
 - 5.Temperature range: -25 ° C-+85 ° C
 - 6.Contact resistance: 10m max
- WAFER


Housing Material: Nylon66 UL 94V0 (2)
 Pin Material: Phosphor Bronze or Brass
 Contact Area Plating: Plated Tin or Plated Gold
 Mates with :P4202-2xXX series Housing
 Poles:02-24P
 Part No.: M4202V-K-2xXX-XX-XX

G=镀金 G3=镀金3U
 无=镀锡
 N2=Pa66-V2
 N0=Pa66-V0
 Pin位数



P. C. B LAYOUT

WWW.XFCNN.COM



CIRCUIT SIZE LAYOUT

| PART NO. | Dimensions (mm) | |
|----------|-----------------|-------|
| | A | B |
| 2x01 | -- | 5.60 |
| 2x02 | 4.20 | 9.80 |
| 2x03 | 8.40 | 14.00 |
| 2x04 | 12.60 | 18.20 |
| 2x05 | 16.80 | 22.40 |
| 2x06 | 21.00 | 26.60 |
| 2x07 | 25.20 | 30.80 |
| 2x08 | 29.40 | 35.00 |
| 2x09 | 33.60 | 39.20 |
| 2x10 | 37.80 | 43.40 |
| 2x11 | 42.00 | 47.60 |
| 2x12 | 46.20 | 51.80 |

| | | | | | | | | | | | |
|-----|--------------|--|------|----------------------------|-------|-------|--------|---|--------------|-------------------------------|------|
| | | | | TOLERANCE UNLESS OTHERWISE | | DRAWN | CK tan | XFCN 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD. | | SHEET | 1/1 |
| | | | | X. | ±0.30 | X° | ±5° | | | CHKD | DATE |
| | | | | .X | ±0.20 | .X° | ±2° | APPD | PRODUCT NAME | 4.20mm Crimp Style Connectors | |
| | | | | .XX | ±0.08 | .XX° | ±1° | VIEW | PART. NO. | M4202V-K-2xXX-XX-XX | |
| AO | MODIFICATION | | DATE | .XXX | ±0.03 | .XXX° | ±0.5° | | | UNITS | mm |
| VER | | | | | | | | | | SCALE | 1:1 |
| | | | | | | | | | | DWG NO. | 009 |