







A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

特性注解:

1. 电气特性:

额定电流: 3 A 最大

工作电压: 20V Max.

介质承受电压: AC 100V /1分钟

绝缘阻抗: 100 MΩ 最小

接触阻抗: 40 mΩ 最大

2. 环境:

工作温度: -40°C~+85°C.

3. 机械特性:

插入力: 5~20Nf.

拔出力: 6~20Nf.

耐久寿命: 5000 Cycles.

4. 盐雾: 24H

3	CONTACT	COPPER ALLOY
2	INSULATOR	HIGH TEMPERATURE PLASTIC UL 94 V-0
1	SHELL	Stainless Steel
NO.	NAME	DESCRIPTION

料号:

TYPE-C-16M-005 普通沉板0.8端子电镀1u"黑色

05/04-19	jack		新增料号		B
09/09-17	jack		NEW-DWG		A
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参考表			东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.		
					TITLE: UUSB TYPE C 16Pin 母头 单排 SMT 外壳短体沉板0.8
X.	±0.15	X.XXX ±0.03	APPD:	PRODUCT NO: TYPE-C-16M-005	
X.X	±0.10	X.X' ±1.00'	CHECK:	DATE	SCALE UNIT TYPE PAGE
X.XX	±0.05	X.XX' ±0.50'	DRAW:	2017.06.09	1:1 mm CD I/1