







Rev.	ECN Number	Description	Date	Drawn	Checked	Approved



技术要求:

1. 材质: 不锈钢 SUS301, T=0.10±0.005;
2. 端子锡脚焊接面和接触面不可有毛边, 其他部位毛边最大 0.03mm;
3. 扭曲: 4.5°/1000mm, 拱形 5mm/1000mm;
4. 标示有“▼”符号的为重点控制和检验尺寸;
5. 未标注之 R MAX R0.13;
6. 电镀须满足 48 小时盐雾测试;
7. 寿命测试 > 2 万次, 产品弹力要求在 60gf ~ 80gf 之间
8. 镍底 50 ~ 80u"min, 产品外表面镀全 1u"MIN

尺寸公差 ±0.05

		GENERAL TOLERANCE XX: ±0.50 X: ±0.35 .X: ±0.25 .XX: ±0.15		SCALE: 1:1		DRAWN CHECK APPROVE		DATE DATE DATE		DWG. NO. 681-0021A-2		TITLE 客户图 RF Antenna Spring, SMT, L3.5*W1.5*H2.5mm		REV. A	
深圳市蝙蝠无线科技有限公司 Shenzhen bats wireless co., LTD		UNIT: mm SIZE: A4		1:1		DATE		DATE		PARTS NO. (INTENDED USE) BW0021AG-L3.5W1.5H2.5		SHEET 1/1			