



技术参数 (SPECIFICATION):

- 温度范围 (TEMPERATURE RANGE): -40~+70℃
- 额定电压 (VOLTAGE RATING): 125V
- 额定电流 (CURRENT RATING): 1.5A
- 接触电阻 (CONTACT RESISTANCE): ≤30mΩ
- 绝缘电阻 (INSULATION RESISTANCE): ≥500MΩ
- 耐压 (DIELECTRIC STRENGTH): 500V AC/(50HZ)/Min
- 插拔力 (MATING AND UNMATING FORCE): 3~20N
- 寿命 (DURABILITY): 750 CYCLES MIN

Table 1

X	Terminal Plating
0	Au Fu" Plating
1	Au 1u" Plating
2	Au 2u" Plating
3	Au 3u" Plating
4	Au 6u" Plating
5	Au 10u" Plating
6	Au 15u" Plating
7	Au 30u" Plating

Material & Plating

Part NO.: RCHSP32-DW-X-XX

LED position

Table 2	
D	L LED/R LED
YG	YELLOW/GREEN
GY	GREEN/YELLOW
YY	YELLOW/YELLOW
GG	GREEN/GREEN
OO	OTHER/OTHER

Material & Color

Table 3	
XX	Material/Color
LB	LCP/BLACK
LW	LCP/WHITE
AB	PA/BLACK
AW	PA/WHITE
OO	OTHER/OTHER

4	外壳	H62	1	NI
3	LED灯	树脂/FE	2	NI/AG
2	插针	PHOSPHOR BRONZE	8	"1U"
1	塑座	LCP	1	BLACK

序号	名称	材料	数量	镀层/颜色	备注
深圳市金航标电子有限公司		WWW.BDS666.COM			
KH-RCHSP32-8P8C-D		0755-83044319			

网络插座外形图

绘图:	日期:
审核:	日期:
核准:	日期:

一般公差		品名:	RCH-SP-32(带灯无弹)
30~	±0.25	料号:	RCHSP32-YGW-1-LB
10~30	±0.20	型号:	RJ45
~10	±0.15	图号:	
角度:	±2°	版本:	
页面:	1 of 1	单位:mm	比例: 1:1

A/0 新出版发行

版次 变更履历

变更单号 绘制 日期

核准: 日期:

