



PART NO. Z-151 ** 00 * 2 8 00 * *

NO. OF CONTACT
 20=20PINS
 28=28PINS
 32=32PINS
 44=44PINS
 52=52PINS
 68=68PINS
 84=84PINS

LOGO
 0=NO LOGO
 1=NEXTRON LOGO

PACK
 0=TUBE
 1=CARRIER TAPE

CONTACT PLATED
 8=MATTE TIN PLATED 150μ"

INSULATOR MATERIAL
 1=PPS
 2=PBT

| No Of Contact | DIM A ±0.25 | DIM B ±0.25 | DIM C ±0.12 | DIM D ±0.12 |
|---------------|-------------|-------------|-------------|-------------|
| 20 | 15.65 | 15.65 | 5.08 | 5.08 |
| 28 | 18.20 | 18.20 | 7.62 | 7.62 |
| 32 | 18.10 | 20.70 | 10.16 | 7.62 |
| 44 | 23.20 | 23.20 | 12.70 | 12.70 |
| 52 | 25.82 | 25.82 | 15.24 | 15.24 |
| 68 | 30.90 | 30.90 | 20.32 | 20.32 |
| 84 | 35.98 | 35.98 | 25.40 | 25.40 |

| REV. | DESCRIPTION | DATE | APPD |
|------|-----------------|----------|--------|
| A4 | ADD 32PINS | 12/25'15 | |
| A3 | PART NO. MODIFY | 2/12'11 | Seawen |
| A2 | PART NO. MODIFY | 11/30'10 | Seawen |

| UNITS <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH | | NAME: PLCC SMT TYPE SOCKET | NEXTRON [®] NEXTRONICS ENGINEERING CORP. | |
|---|--------------------|-------------------------------|--|------------|
| GENERAL TOLERANCES: (UNLESS SPECIFIED) | | PART NO: Z-151**00*2800** | TITLE: CUSTOMER DWG | |
| 4 PLACE ±** ±** | 3 PLACE ±** ±** | APPD: 楊海文 12/25'15 | DWG NO: 010-0000-581 | C |
| 2 PLACE ±0.10 ±.** | 1 PLACE ±0.20 ±.** | CHKD: 廖小瓊 12/25'15 | SCALE: 1/1 | SHEET: 1/1 |
| ANGULAR: X°±2° X°±** | | DRAWN: 陳惠枝 12/25'15 | REV.: | A4 |