



part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note
silver plated	gold plated		mm²	AWG			
09 15 000 6207	09 15 000 6227	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool adjusting Ø0,1
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22		09 99 000 0110 09 99 000 0021	
09 15 000 6203	09 15 000 6223	1,10	0,5	20		09 99 000 0888 09 99 000 0001 09 99 000 0110 09 99 000 0021	
09 15 000 6205	09 15 000 6225	1,30	0,75	18			
09 15 000 6202	09 15 000 6222	1,45	1	18			
09 15 000 6201	09 15 000 6221	1,75	1,5	16			
09 15 000 6206	09 15 000 6226	2,25	2,5	14		6	



All Dimensions in mm
Original Size DIN A4

Scale
2:1

Free size tol.

Ref.

Sub.



All rights reserved

Department EL PD - DE

HARTING Electric GmbH & Co. KG

D-32339 Espelkamp

Created by
RULLKOETTER

Inspected by
SCHNIEDER

Standardisation
RUETERA

Date
2018-05-29

State
Final Release

Title

Han D crimp contacts female

Doc-Key / ECM-Nr.
100109246/UGD/004/B
500000135752

Type

TB

Number

09 15 000 62XX

Rev.

B

Page

1/1