


THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.



Customer Drawing




注 (NOTES):

1. 对配母端直径 Suitable Socket diameter: 1.0mm
2. 额定电流 Current rating: 5A
3. 端子类型 Terminatin type: Crimp
4. 压线规格: AWG20~22
5. 电镀信息 Plating specification: See below
 - 5.1. 当 XX=01 镍底, 整个端子飘金.
When XX=01 Gold flash plate overall.
 - 5.2. 当 XX=02 镍底, 接触位置镀金10u"
When XX=02 Contact plating 10u"
 - 5.3. 当 XX=03 镍底, 接触位置镀金30u"
When XX=03 Contact plating 30u"
 - 5.4. 当 XX=04 镍底镀锡
When XX=04 Tin over nickel
6. 材料规格 Material specification:
 - 6.1. 端子: 铜合金
Contact body: Copper alloy
 - 6.2. 外套: 不锈钢
Oter spring: Stainless steel
7. 符合ROHS
ROHS compliance

REVISIONS					
REV	ZONE	ECO	DESCRIPTION	DATE	BY APPR
A	--	--	INITIAL RELEASE	12/01/14	RW EC
B	--	--	料号更改从HCTM20XX改为HCTM120XX	01/28/15	RW EC



SECTION
A-A



SECTION
B-B

AMPHENOL TP	Amphenol Technical Products International GZ					
	第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	
签名 SIGNATURE		日期 DATE	UNLESS OTHERWISE SPECIFIED			PART NAME:
制图 DRAWN	RW	12/01/14	1) All dimensions are in metric(mm). 2) Tolerances are as follows: 0 PL DEC ± 1.00 1 PL DEC ± 0.50 2 PL DEC ± 0.20			HC Contect 20#Pin 20~22AWG
审核 CHECKED	GX	12/01/14	Angles $\pm 1^\circ$			DWG NO:
批准 APPROVAL	EC	12/01/14				HCTM120XX
						CUST PART #:
						N/A
						CUST REV.
						-