


RoHS




SPECIFICATIONS

Rated Current:1.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Phosphor Bronze
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



W= With Post

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司				
				X.X	±0.30			UNIT	mm							
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		FH-00186				
A0				2012.04.18	NEW DRAWING				SHEET	1/1	TITLE:		1.27FH 2x14Pin H4.3 SMT 蘇維			
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	±3'	APPROVE	PROJ.								
DIM	TOL															
1	2	3	4	5	6	7	8	9								