



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance:  $20\text{m}\Omega$  Max
- 5、Insulation Resistance:  $1000\text{M}\Omega$  Min
- 6、Withstanding Voltang:  $1000\text{V AC/minute}$
- 7、Material: Wafer LCP、PA6T、UL94V-0  
PIN Brass Tin-plated  
Solder tad Brass Tin-plated

编号	尺寸 (mm)		
	A	B	C
XH-2AWT	2.50	7.50	10.00
XH-3AWT	5.00	10.00	12.50
XH-4AWT	7.50	12.50	15.00
XH-5AWT	10.00	15.00	17.50
XH-6AWT	12.50	17.50	20.00
XH-7AWT	15.00	20.00	22.50
XH-8AWT	17.50	22.50	25.00
XH-9AWT	20.00	25.00	27.50
XH-10AWT	22.50	27.50	30.00
XH-11AWT	25.00	30.00	32.50
XH-12AWT	27.50	32.50	35.00
XH-20AWT	47.50	52.50	55.00

**PCB LAYOUT**

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	XH-NAWT		版本 REV.	A			
			X.±0.25	X.'±2'		2013、07、01	客户料号 CUTM. NO.		版次 SHEET	1/1					
			.X±0.20	.X'±1'									审核 CHECK	张名	
			.XX±0.15	.XX'±0.5'										核准 APPROVAL	张名
.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1			深圳市华灿天禄电子有限公司							