


SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Brass Tin-plated
Solder Phosphoric bronze Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
HY-2ALT	2.00	8.00
HY-3ALT	4.00	10.00
HY-4ALT	6.00	12.00
HY-5ALT	8.00	14.00
HY-6ALT	10.00	16.00
HY-7ALT	12.00	18.00
HY-8ALT	14.00	20.00
HY-9ALT	16.00	22.00
HY-10ALT	18.00	24.00
HY-11ALT	20.00	26.00
HY-12ALT	22.00	28.00
	38.00	44.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	HY-NALT		版本 REV.	A						
			X.±0.25	X.*±2'		2013、07、01	张名		品名 TITLE	HY立贴 WAFER SMT TYPE			页次 SHEET	1/1				
			.X±0.20	.X*±1'											2013、07、03	张名	客户料号 CUTM. NO.	富港电子
			.XX±0.15	.XX*±0.5'														
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1													