



**SPECIFICATIONS**

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 1400V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 3800V AC/minute
- 7、Material: Wafer Nylon6T, UL94V-0  
PIN Brass Tin-plated  
Solder tad Phosphoric bronze Tin-plated

**PCB LAYOUT**

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	HYGC-3.5-01		版本 REV.	A		
			X.±0.25	X.*±2'		2013、07、01			品名 TITLE	BH3.5贴片		页次 SHEET	1/1	
			.X±0.20	.X*±1'		2013、07、03				WAFER SMT TYPE				
			.XX±0.15	.XX*±0.5'		2013、07、05				客户料号 CUTL. NO.			富港电子	
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1									