


1	2	3	4	5	6	7	8
REVISION		DESCRIPTION		DATE		DRAFTER	
A0		FIRST RELEASE		18.11.29		Mark	



技术要求:

1. 两端SMA 接头朝向需一致
2. 特性阻抗:50Ω; 适用频率范围:DC-6GHz, VSWR<1.5;
3. 断短路与高压测试: 100%使用线材综合测试仪测试。
测试条件: 断短路判定值:2kΩ; 直流导通电阻:最大2.00Ω; 绝缘电阻:DC 300V, 0.05秒, 50MΩ。
4. 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
5. 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
6. 1 PCS/袋, 不能用印有皇捷字的纸箱包装
7. 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

COMPLIANCE WITH THE REQUIREMENT: ■ RoHS; □ HF; □ SONY SS-00259; □ OTHERS H470
*NO USING ESTRUCTED AND BANNED SUBSTANCE

5	2TA030BK1-011	黑色热缩套管, OD:3.0*L11.0, 严格依11裁切	2	---
4	2LC15PM029-7	OD:5.0*1.0上盖, 镀金	1	---
3	2LC15PM029-6	OD:4.85*0.5, TPE, 绝缘粒	1	---
2	2LC15PM029-1	SMA R/A Male FOR RG316D CABLE	1	---
1	2C5R31623BN4	RG316D, 透明棕双编双银同轴电缆, OD:2.9	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS

GENERAL TOLERANCE: LINEAR: X ±1.0 X.X ±0.50 X.XX ±0.20 X.XXX ±0.10 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司 手机: 15015262131/13714786106	
FILE NAME: 产品图	TITLE: 射频转接线组件	SMA R/A Mele to SMA R/A Male with RG316D L:150mm cable assembly CA-316SMA5M15CM	
ENG/DATE: Mark/18.11.29	CHE/DATE:	P/N: RG316-SMA-L=150mm	
APP/DATE:	UNIT: mm	SCALE: 1:1	REVISION: A0
			SHEET: 1/1