





SYM	ECN No.	MODIFICATION	DATE	ISSUED



Note:

## 1.Material:

1.1,Housing: High temperature

thermoplastic with/black g.f,UL94v-0

1.2,Contact: copper alloy,t=0.25mm

1.3,Shell: copper/Ferroalloy alloy,t=0.35mm

## 2.Specification:

2.1,Current rating:3A Max.

2.2,Dielectric withstanding

voltage: 100 V(ac) for 1 min.

2.3,Contact resistance: 30 mΩ Max.

2.4,Insulation resistance: 100 MΩ Min.

2.5,Total mating force: 3.57 Kgf Max.

2.6,Total unmating force: 1.0 Kgf Min.

## 3.Finish:

3.1,Contact: Plated Gold in Mating Area:

Tin On Solder Talls

Shell: Nickel Plating

## 4.Environmental:

4.1,Temperature range: -55°C~85°C

DRAWN		<b>JTJ</b> 深圳市精拓金电子有限公司			
CHECKED		TITLE		PART NO.	
APPROVED		AM大电流一体式（大縫隙） PBT白色/5A		917-111A101DAM0400	
3rd ANGLE PROJECTION		TOLERANCE		SCALE	SHEET
UNIT		.XXX±.10, .XX±.15, .X±.25, ANG±1°		1:1	1 OF 1
mm				SIZE	REV.
				A4	X1