



| | | |
|------|--------------|------|
| MAPX | MODIFICATION | DATE |
| | | |

特性: Specifications:

电气: Electrical:

1. 接触阻抗: Contact Resistance:
30 milliohms MAX
2. 耐电压: Dielectric With Standing Voltage:
250 V AC AT Sea Level
3. 绝缘阻抗: Insulation Resistance:
1000 MEGA ohms MIN

机构: Mechanical:

1. 结合力: Mating Force:
35 N MAX 最大 35 N
2. 拔出力: Unmating Force:
8 N MIN 最小 8 N

材料: Material:

1. 塑胶: PBT.
2. 端子: Contact: C2680, T=0.25±0.01
3. 外壳: Shell: C2680, T=0.3±0.01

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area:
Tin/Lead On Solder Talls. 接触点镀金1唛, 脚镀锡100唛
2. 外壳: Shell:
Nickel Plating . 镀镍80唛

额定电流3A/宽PIN, 1.5A/窄PIN, 盐雾48H, 镀锡部分盐雾12H.

| | | | | | | | | | | |
|-------------------------------------|-------|------|-------|--------------|------------|---------------|-----|--------------------------|---|----|
| 产品图 PRODUCT CHART DWG | | | | 深圳市精拓金电子有限公司 | | | | | | |
| 公差一览表 TOLERANCE UNLESS OTHERWISE | | | | 单位 UNITS | MM | 制图 DRAWING | 尹先华 | 制图料号 PRODUCT PART NO. | 912-212A101CD10200 | |
| X. | ±0.25 | X. | ±5.° | 比例 SCALE | 1:1 | 审核 CHKD | 郭治富 | 产品名称 PRODUCT NO. | AF10.6短体大电流前卷脚后鱼叉脚有边铜壳 PBT白胶10.5 DIP | |
| .X | ±0.20 | .X | ±2.° | 日期 DATE | 2021-04-13 | 核准 APPD | 黄国荣 | 角法 VIEW | 版本 VER | A0 |
| .XX | ±0.15 | .XX | ±1.° | | | | | | | |
| .XXX | ±0.10 | .XXX | ±0.5° | | | | | | | |