



RoHS

MAPX




MODIFICATION

DRW

DATE



PCB LAYOUT



特性: Specifications:

电气: Electrical:

- 1. 接触阻抗: Contact Resistance: 30 milliohms MAX
- 2. 耐电压: Dielectric With Standing Voltage: 500 V AC AT Sea Level
- 3. 绝缘阻抗: Insulation Resistance: 1000 MEGA ohms MIN

机构: Mechanical:

- 1. 结合力: Mating Force: 35 N MAX 最大 35 N
- 2. 拔出力: Unmating Force: 8 N MIN 最少 8 N

材料: Material:

- 1. 塑胶: 黑色PBT.
- 2. 端子: Contact: C2680, T=0.25 ± 0.01
- 3. 外壳: Shell: SPCC, T=0.3 ± 0.01

电镀: Finish:

- 1. 端子: Contact: Plated Gold in Mating Area: Tin/Lead On Solder Talls. 接触点镀金1唛, 脚镀锡100唛
- 2. 外壳: Shell: Nickel Plating . 镀镍80唛 额定电流2.5A, 盐雾24H, 镀锡部分12H

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.25	X.	±5.°
.X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.10	.XXX	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	尹先华	制图料号 PRODUCT PART NO.	912-122A102AD10200
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AF10.6短体前两脚无边铜壳PBT黑胶8.2 DIP
日期 DATE	2021-04-14	核准 APPD	黄国荣	角法 VIEW	版本 VER
					A0