







MAPX	MODIFICATION	DATE



TOLERANCE: ± 0.05 ,
RECOMMENDED PCB LAYOUT
(TOP VIEW)

NOTES:

- 1.MATERIAL:
 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC.
 1.2 SPRING CONTACT: COPPER ALLOY.
 1.3 FLAT CONTACT: COPPER ALLOY
 1.4 SHELL :COPPER ALLOY.
 1.5 COVER:HIGH TEMPERATURE THERAL PLASTIC.
- 2.FINISH:
 2.1 CONTACT: (SEE P/N.),[50 μ] MIN. NICKEL UNDERPLATING OVER ALL.
 2.2 SHELL: [50 μ] MIN.SOLDERABLITY NICKEL UNDERPLATING OVER ALL.



PIN NO.	PIN 1	PIN 2	PIN 3	PIN 4
SLGNAL NAME	V BUS	D-	D+	GND
REMARK	USB 2.0 CONTACT PINS			

PIN NO.	PIN 5	PIN 6	PIN 7	PIN 8	PIN 9
SLGNAL NAME	STDA_SSRX-	STDA_SSRX+	GND_DRAIN	STDA_SSTX-	STDA_SSTX+
REMARK	USB 3.0 CONTACT PINS				

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司								
公差一览表 TOLERANCE UNLESS OTHERWISE		单位	MM	制图	尹先华	制图料号	916-162A2058Y20200			
X.	± 0.25	X.	$\pm 5.^\circ$	比例	郭治富	产品名称	AF3.0 180度15.0弯脚无边铜壳LCP蓝胶			
.X	± 0.20	.X	$\pm 2.^\circ$	日期	黄国荣	角法			版本	AO
.XX	± 0.15	.XX	$\pm 1.^\circ$	DATE	2021-04-14	核淮	APPD	VER		
.XXX	± 0.10	.XXX	$\pm 0.5^\circ$							