



1 2 3 4 5 6 7 8 9 10




MAPX	MODIFICATION	DATE

A
B
C
D
E
F
G

A
B
C
D
E
F
G



RECOMMENDED P.C.B LAYOUT



规格型号: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗: Contact Resistance
30 milliohms MAX
- 介电耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

- 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
- 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

- 塑膠: Housing:
Hing Temperature Ternmaplastics,
PBT\LCP White/Black
- 端子: Contact: Copper Alloy C2680
- 外圍: Shell: Copper Alloy C2680/SPCC

- 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Talls
- 端子四周鍍50U”(MIN)鍍,鍍金区域鍍100-200U”鍍金 1U”
總圖四周鍍80U”(MIN)鍍
Nickel Plating

<p>产品图 PRODUCT CHART DWG</p>				<p>深圳市精拓金电子有限公司</p>						
<p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				单位 UNITS	MM	制图 DRAWING	尹先华	制图料号 PRODUCT PART NO.	917-P81A202ED60201	
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AM90度沉板短直脚铁壳带柱LCP黑胶24H	
.X	±0.20	.X	±2.°	日期 DATE	2021-04-15	核准 APPD	黄国荣	角法 VIEW	版本 VER	AO
.XX	±0.15	.XX	±1.°							
.XXX	±0.10	.XXX	±0.5°							

1 2 3 4 5 6 7 8 9 10