






MAPX	MODIFICATION	DATE



SECTION A-A


Note:

1.Material:

- 1.1 Housing: High temperature thermoplastic with g.f,UL94v-0
- 1.2 Contact: copper alloy,t=0.20mm
- 1.3 Shell: copper alloy or sus,t=0.25mm

2.Specification:

- 2.1 Current rating:1,5PIN 1.8A Max/2,3,4PIN 1A Max.
- 2.2 Dielectric withstanding voltage: 100 V(ac) for 1 min.
- 2.3 Contact resistance: 30 mΩ Max.
- 2.4 Insulation resistance: 100 MΩ Min.
- 2.5 Total mating force: 3.57 Kgf Max.
- 2.6 Total unmating force: 1.0 Kgf Min.
- 2.7 Temperature range: -30°C~80°C



RECOMMENDED PCB LAYOUT

PCB图仅供参考

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司					
公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	Gavin	制图料号 PRODUCT PART NO.	920-B52A2021S10104
X.	±0.35	X.	±5.°	比例 SCALE	1:1	审核 CHKD	郭治富
.XX	±0.20	.XX	±1.°	日期 DATE	2016-06-05	核准 APPD	黄国荣
.XXX	±0.10	.XXX	±0.5°	角法 VIEW		版本 VER	A0
						产品名称 PRODUCT NO.	MICRO 5S B型两脚插板6.4有边有柱加焊脚 短端SMT镀镍