



MAPX	MODIFICATION	DATE
------	--------------	------

- 特性: Specifications
 电气: Electrical:
- 接触阻抗: Contact Resistance
30 milliohms MAX
 - 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
 - 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

- 机构: Mechanical:
- 结合力: Mating Force:
4.0KG NAX 最大4kg
 - 拔出力: Unmating Force:
0.5 KG NIN 最少0.5kg

- 材料: Material:
- 塑胶: Housing: High Temperature Thermoplastic
 - 端子: Contact: Copper Alloy 铜合金
 - 外壳: Shell: Copper Alloy 铁/铜合金

- 电镀: Finish:
- 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tail
接触点镀金. 脚镀锡
 - 外壳: Shell:

Nickel Plating 镀镍

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司						
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	907-152A1022D10200	
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD	L-Y-J	产品名称 PRODUCT NO.	AF90度17.0双层半包弯脚有边双弹 铜壳PBT黑胶	
.X	±0.20	.X	±2.°	日期 DATE	2014.06.09	核准 APPD	L-Y-J	角法 VIEW	版本 VER	A0
.XX	±0.15	.XX	±1.°							
.XXX	±0.10	.XXX	±0.5°							