



目錄 MAPX	設變內容 MODIFICATION	日期 DATE



PCB LAYOUT

NOTES:
Housing: Thermoplastics,UL94V-0
Contact: Copper Alloy
Shell: Copper Alloy/Steel
Voltage Current Rating:1.5 AMP. 30V AC
Insulation Resistance:1000MΩ Min.
Contact Resistance:30 MΩ Max.
Dielectric Withstanding Voltage:500V AC
Temperature Range:-35°C to +85°C
Insulator color: Black/White
Plastic material:PBT/LCP/Others
Shell finish:Nickel plated/Tin-Lead plated
Mechanical:
Mating Force: 3.5KG MAX
Unmating Force: 0.7 KG MIN.
Contact finish:
01: Selective Gold Flash
02: Selective Gold 3U"
03: Selective Gold 5U"
04: Selective Gold 15U"
05: Selective Gold 30U"

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司					
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.	903-152A1012D10100
X.	±0.25	X'	±5'	比例 SCALE	1:1	审核 CHKD	日期 DATE	产品名称 PRODUCT NO.	AF90度无后盖鱼叉脚有边内弹 14.0铜壳T型PBT白胶
.X	±0.20	.X'	±2'						
.XX	±0.15	.XX'	±1'	核准 APPD	2015.03.14	角法 VIEW	版本 VER	A0	
.XXX	±0.10	.XXX'	±0.5'						