



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 500MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer PBT, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
ZH1.5-2AW	1.50	4.50
ZH1.5-3AW	3.00	6.00
ZH1.5-4AW	4.50	7.50
ZH1.5-5AW	6.00	9.00
ZH1.5-6AW	7.50	10.50
ZH1.5-7AW	9.00	12.00
ZH1.5-8AW	10.50	13.50
ZH1.5-9AW	12.00	15.00
ZH1.5-10AW	13.50	16.50
ZH1.5-11AW	15.00	18.00
ZH1.5-12AW	16.50	19.50
ZH1.5-13AW	18.00	21.00
ZH1.5-14AW	19.50	22.50
ZH1.5-15AW	21.00	24.00
ZH1.5-16AW	22.50	25.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	ZH1.5弯针		版本 REV.	A				
			X.±0.25	X.*±2'		2013.07.01	品名 TITLE		ZH直针 WAFER DIP TYPE	页次 SHEET			1/1			
			.X±0.20	.X*±1'										2013.07.03	客户料号 CUTL. NO.	
			.XX±0.15	.XX*±0.5'												
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1											

4 1 8 0 0 0 0 0 0 0