










版数 REV.	年月日 DATE	図 NO.	変更内容 DESCRIPTION	製 図 DR.	担 当 CHK.	査 閲 APPD.	承認 APPD.
3	29/JUN/2012	002873	REDRAWN	T. ENOMOTO	Y. WATANABE	—	A. ONO



NOTE1. FEMALE-COUNTERPART CONNECTOR : MX34020SF1 (SJ038752)
2. APPLICABLE SCREW : JIS B 1122 CROSS RECESSED HEAD TAPPING SCREW M3×6, CLASS 2 (TYPE B)

注 1. かん合相手メスコネクタ : MX34020SF1 (SJ038752)
2. 推奨取付ネジ JIS B 1122 十字穴付なベタッピンネジ 2種 M3×6

3	TERMINAL-L2	10	BRASS	PLATING: Sn	MATERIAL-PLATING
2	TERMINAL-L1	10	BRASS	PLATING: Sn	MATERIAL-PLATING
1	HOUSING	1	SPS-GF30		COLOR: GRAY
符号 NO.	名 称 DESCRIPTION	個 数 (QTY)	材 質 MATERIAL	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION) JACS-1754 JABL-1754		第1版 (ORIGINAL DATE) 26/JUN/2003		尺 寸 (SCALE) 2:1	シ リーズ (SERIES) MX34
一般公差 (GENERAL TOLERANCE)		製 図 DR.	日本航空電子工業株式会社		
寸法 (DIMENSION)		担 当 CHK.	JAE JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.		
角 度 (ANGLES)		査 閲 APPD.	図面番号 (DRAWING NO.)		
. ± 0.8		承認 APPD.	SJ038751		
. × ± 0.4			質量 (MASS)		
. × × ± 0.1			5.6g		
. × × × ±					