


12	13	14	15
MAPX	MODIFICATION	DATE	DRAW






NOTES:

- 1.MATERIAL:  
HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V\_0  
CONTACT: COPPER ALLOYS.  
COVER: COPPER ALLOYS OR STEEL.
- 2.PLATING:  
UNDERPLATE: NICKEL.

SPECIFICATIONS:

- Voltage Rating:125V AC DC
- Current Rating:1A AC,DC
- Withstanding voltage:500V AC 1/Minute
- Insulation Resistance:100MΩ Min
- Contact Resistance:20mΩ Max
- Temperatuer Range:-25℃ ~+ 85℃



RECOMMENDED P.C.B HOLE LAYOUT

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	TITLE:	
UNLESS OTHERWISE SPECIFIED TOLERANCES			PAR	WAFER-200W-4P
DECIMALS:	ANGLES:	DWN		
X.X:±0.35	X.X':±3°	CHKD		
X.XX:±0.25	X.XX:±2'	APVD		
X.XXX:±0.15		SCALE1:1	UNIT:MM	⊕
		CUSTOMER COPY	SIZE:A4	SHEET:1F1
				REV:A