









PCB LAYOUT



7~9A



10~16A

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer PBT, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
PA-2AWD	2.00	6.00
PA-3AWD	4.00	8.00
PA-4AWD	6.00	10.00
PA-5AWD	8.00	12.00
PA-6AWD	10.00	14.00
PA-7AWD	12.00	16.00
PA-8AWD	14.00	18.00
PA-9AWD	16.00	20.00
PA-10AWD	18.00	22.00
PA-11AWD	20.00	24.00
PA-12AWD	22.00	26.00
	30.00	34.00

GENERAL TOLERANCE		制 图 DRAWING	钱 岳 生 2021、05、03			料 号 PART NO.	PA-NAW	版 本 REV.	A
X.±0.25	X.±2°		审 核 CHECK			品 名 TITLE	PA弯针 WAFER DIP TYPE	页 次 SHEET	1/1
.X±0.20	.X.±1°	核 准 APPROVAL	张 名 2021、05、04			客 户 料 号 CUTM. NO.			
.XX±0.15	.XX.±0.5°		张 名 2021、05、05						
.XXX±0.10	.XXX.±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1	富 港 电 子			