


SPECIFICATION FOR APPROVAL


CUSTOMER		CUST P/N.	
ITEM	Toroidal Coil Inductors	Description	TM040202N-251-M
PART NO.	302-74769	DATE	

(1) DIMENSION(UNIT:mm)



Marking(印字):PIN1脚打白点,印白色" 251"印字要采用镭射激光

SCHEMATIC



A	9.5(Max)	mm
B	6.0(Max)	mm
C	5.0(Max)	mm
D		mm
E		mm
F		mm
G		mm
H		mm
I		mm

(2)ELECTRICAL REQUIREMENTS

TEST CONDITION		FREQUENCY	(3) TEST INSTRUMENTS	
		VOLTAGE	LCR-METER:	
L1=L2	250uH±30%	100KHz 0.05V		HP-4291A
DCR1=DCR2	130mΩ(Max)	KHz V	DC RESISTANCE METER:	
			V	WK3260B
I _{rms}	1.2A(Max)at△T=40℃(TYP)	KHz V	CURRENT SOURCE:	
			V	TH2816+1320
HP(L1TOL2)	1500V/DC/3mA/2Sec			9073A

(4)TURN:10TS(REF)

(5)MATERIAL LIST

ITEM	MATERIAL	DESCRIPTION
1	CORE	N10 T3.9*2*2-P大冶
2	WIRE	Ø0.15mm(2UEW-H)N 益利素勒
		Ø0.15mm(2UEW-H)R益利素勒
3	VARNISH	BC-359
4	BASE	UBL023-4

REMARK:	APPROVED	CHECKED	DRAWN BY

MINGSTAR ELECTRONIC CORP.