






环保要求 RoHS 2.0

NOTES:
1.MATERIAL:
 HOUSING:THERMOPLASTIC(UL94V-0) NATURE
 ACTUATOR:THERMOPLASTIC(UL94V-0) BLACK
 TERMINAL:PHOSPHOR BRONZE PLATED GOLD MIN 1u" FOR SOLDERING
 AREA AND CONNECT AREA, PLATED NI MIN 30u" FOR
 ALLOVER UNDER.
 FITTING NAIL:PHOSPHOR BRONZE MATTE TIN MIN 80u" PLATED FOR
 ALLOVER PLATED NI MIN 30u" FOR ALLOVER UNDER.
2.SPECIFICATION
 CURRENT RATING: 0.5A 50VAC/DC
 CONTACT RESISTANCE: 30mΩ MAX
 INSULATION RESISTANCE: 100MΩ MIN AT 500V DC
 OPERATING TEMPERATURE RANGE: -25°C TO +85°C
 WITHSTANDING VOLTAGE: 500V AC/minute




PCB LAYOUT REF

TOLERANCE: ± 0.05



SECTION A-A
SCALE 2:1



RECOMMENDED FFC DIM.
WITH LOCK

深圳市钜硕电子有限公司 SHENZHEN JUSHUO ELECTRONIC CO., LTD				产品料号 : AFC18-S68FIA-00					
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE XX ±0.30 XXX ±0.20 XXXX ±0.10 ANG. ±1°				APPROVED BY	DATE	TITLE FPC CONN. 0.5P H1.8			
				CHECKED BY	DATE	FLIP TYPE 68Pin 成品图			
				DRAWN BY	DATE	DOCUMENT NO			
UNIT MM		SIZE A4	DRAWING NO			REV A	SHEET 1/1	SCALE 1:1	
TION	CHK	DATE							