









further more information
see DS 09181100001

full range of P/N's and
dimensions shown on page 2/2

coding style table	
	style A: for connectors 6-pole
	style B: for connectors from 10 to 14-pole
	style C: for connectors from 16 to 64-pole

		All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol. IEC 60603-13	Ref. Sub. TB 09185XXX324 / 500000068837 / 2014-05-16		
				Created by STORCK	Inspected by LEHNERT	Standardisation HOFFMANN	Date 2015-12-07	State Final Release
		All rights reserved Department EC PD - DE		Title SEK 18 male low profile straight solder 2.9			Doc-Key / ECM-Nr. 100154466/UGD/008/A 500000094890	
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 09185XXX324				Rev. A	Page 1/2

1	2	3	4	5	6	7	8			
A								A		
B								B		
C		performance level			insulator colour	dimensions				
	no. of contacts	PL3	PL2	S4		A max.	B	E		
	06	09 18 506 7324	09 18 506 6324	09 18 506 5324		15,4	12,78	2,54 x 2 = 5,08		
	10	09 18 510 7324	09 18 510 6324	09 18 510 5324		20,5	17,86	2,54 x 4 = 10,16		
	14	09 18 514 7324	09 18 514 6324	09 18 514 5324		25,6	22,94	2,54 x 6 = 15,24		
	16	09 18 516 7324	09 18 516 6324	09 18 516 5324		28,1	25,48	2,54 x 7 = 17,78		
	20	09 18 520 7324	09 18 520 6324	09 18 520 5324		33,2	30,56	2,54 x 9 = 22,86		
	26	09 18 526 7324	09 18 526 6324	09 18 526 5324		40,8	38,18	2,54 x 12 = 30,48		
	30	09 18 530 7324	09 18 530 6324	09 18 530 5324		45,9	43,26	2,54 x 14 = 35,56		
	34	09 18 534 7324	09 18 534 6324	09 18 534 5324		51,0	48,34	2,54 x 16 = 40,64		
	40	09 18 540 7324	09 18 540 6324	09 18 540 5324		58,6	55,96	2,54 x 19 = 48,26		
	50	09 18 550 7324	09 18 550 6324	09 18 550 5324		71,5	68,66	2,54 x 24 = 60,96		
	60	09 18 560 7324	09 18 560 6324	09 18 560 5324		84,2	81,36	2,54 x 29 = 73,66		
	64	09 18 564 7324	09 18 564 6324	09 18 564 5324		89,3	86,44	2,54 x 31 = 78,74		
D	06	09 18 506 7324 001	09 18 506 6324 001	09 18 506 5324 001	black	15,4	12,78	2,54 x 2 = 5,08		
	10	09 18 510 7324 001	09 18 510 6324 001	09 18 510 5324 001		20,5	17,86	2,54 x 4 = 10,16		
	14	09 18 514 7324 001	09 18 514 6324 001	09 18 514 5324 001		25,6	22,94	2,54 x 6 = 15,24		
	16	09 18 516 7324 001	09 18 516 6324 001	09 18 516 5324 001		28,1	25,48	2,54 x 7 = 17,78		
	20	09 18 520 7324 001	09 18 520 6324 001	09 18 520 5324 001		33,2	30,56	2,54 x 9 = 22,86		
	26	09 18 526 7324 001	09 18 526 6324 001	09 18 526 5324 001		40,8	38,18	2,54 x 12 = 30,48		
	30	09 18 530 7324 001	09 18 530 6324 001	09 18 530 5324 001		45,9	43,26	2,54 x 14 = 35,56		
	34	09 18 534 7324 001	09 18 534 6324 001	09 18 534 5324 001		51,0	48,34	2,54 x 16 = 40,64		
	40	09 18 540 7324 001	09 18 540 6324 001	09 18 540 5324 001		58,6	55,96	2,54 x 19 = 48,26		
	50	09 18 550 7324 001	09 18 550 6324 001	09 18 550 5324 001		71,5	68,66	2,54 x 24 = 60,96		
	60	09 18 560 7324 001	09 18 560 6324 001	09 18 560 5324 001		84,2	81,36	2,54 x 29 = 73,66		
	64	09 18 564 7324 001	09 18 564 6324 001	09 18 564 5324 001		89,3	86,44	2,54 x 31 = 78,74		
	E								E	
	F								F	
1	2	3	4	5	6	7	8			

	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department EC PD - DE	STORCK	LEHNERT	HOFFMANN	2015-12-07	Final Release	
HARTING Electronics GmbH		Title				Doc-Key / ECM-Nr.	
D-32339 Espelkamp		SEK 18 male low profile straight solder 2.9				100154466/UGD/008/A 500000094890	
		Type	Number			Rev.	Page
		TB	09185XXX324			A	2/2



All rights reserved
Department EC PD - DE



All Dimensions in mm
Original Size DIN A3

Scale
1:1

Free size tol.

Created by
STORCK

Inspected by
LEHNERT

Standardisation
HOFFMANN

Date
2015-12-07

State
Final Release

Title
SEK 18 male low profile straight solder 2.9

Type
TB

Number
09185XXX324

Doc-Key / ECM-Nr.
100154466/UGD/008/A
500000094890

Rev.
A

Page
2/2

HARTING Electronics GmbH
D-32339 Espelkamp

Ref.
Sub. TB 09185XXX324 / 500000068837 / 2014-05-16